

## Stahlwille Torque wrenches 730N N/65



Article number	G0603.300.065
Brand	-
UBB	500503929977
UNSPSC	27111715
EAN	4018754163991
PKG. of 1	Full Box Only

### Technical Parameters

Connection type	Tool carrier
Driving	14X18
Reach (Nm)	130-650 NM
Torque type	mechanical
Type nr.	730N
Version (torque)	click

### Standards

Info	<p>Torque Wrenches offering quick adjustment, with cut-out, with QuickRelease safety lock (size 5-65) dual signal (size 2-40), dual scale Nm/ft.lb. resp. Nm/inch.lb. (size 5-80), long term accuracy and facility to accept insert/shell tools. The robust steel tube completely encloses all working parts. Even when misused (slackening sized bolts, for example), the measuring element remains stress free. Reversible insert/shell tools allow anticlockwise operation. Recalibration--</p>
------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

without dismantling--  
with the aid of  
checking gauges No.  
798, No. 799 or No.  
7707 W. Guaranteed  
accuracy  $\pm 4\%$ . With  
certificate.