

Stahlwille Torque wrenches 730DR DR/65 DIG



Article number	G0603.800.065
Brand	-
UBB	500511614827
UNSPSC	27111715
EAN	4018754187638
PKG. of 1	Full Box Only

Technical Parameters

Connection type	Ratchet
Driving	3/4
Reach (Nm)	65-650 NM
Torque type	electro-mechanical
Type	QuickRelease
Type nr.	730DR
Version (torque)	click/measuring

Info

Torque Wrenches offering quick adjustment, with cut-out, with QuickRelease safety lock (size 5-65) dual signal (size 2-40), dual scale Nm/ft.lb. resp. Nm/inch.lb. (size 5-80), long term accuracy and facility to accept insert/shell tools. The robust steel tube completely encloses all working parts. Even when misused (slackening sized bolts, for example), the measuring element remains stress free. Reversible insert/shell tools allow anticlockwise

Standards



operation.
Recalibration--
without dismantling--
with the aid of
checking gauges No.
798, No. 799 or No.
7707 W. Guaranteed
accuracy $\pm 4\%$. With
certificate.