



Lever clamp GH clamping width 400 mm radius 120 mm clamping force up to 8500 N B

Article number	K0441.000.040
Brand	-
UBB	240180131775
UNSPSC	31162903
EAN	4008158034447
PKG. of 1	Full Box Only

Technical Parameters

Chucking range	400 - 400
Jaw length	120
With antislip facility	Yes

Standards