



KNIP FLAT NOSE PL 20 2005-140MM

Article number	K1020.500.140
Brand	-
UBB	419100021734
UNSPSC	27112126
EAN	4003773042464
PKG. of 1	Full Box Only

Technical Parameters

Total length (mm)	140
Type nr.	2005140
Version (pliers & tweezers)	Chrome plated & with multi-component grips

Standards

ISO	5745
-----	------

Info

Short, flat jaws. Serrated gripping surfaces. Special tool steel, oil-hardened and tempered. Finish 1 = Head polished. Handles plastic coated. Finish 2 = Head polished. Handles with two-colour dual component sleeves. Finish 5 = Plier chrome plated. Handles with two-colour dual component sleeves. Finish 6 = Plier chrome plated. Handles insulated with two-colour dual component sleeves 1000 V VDE-tested DIN EN/IEC 60900. Finish 7 = Plier chrome plated.



Handles dipped
plastic insulated
1000 V VDE-tested
DIN EN/IEC 60900.