



Kinkelder Circular saw blade 315X2,5X40T10 4/12

Article No.	K6000.341.410
Brand	-
UBB	240146013067
UNSPSC	23242113
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Application (metal)	Steel
Arbor size (mm)	40
Blade diameter (mm)	315
Model	Alpha
Tooth pitch	10
Thickness	2.5 mm
Pinholes	2/8,5/55 4/12/64

Standards