



1/4" - 3/8" RATCHET KIT IN BLOWCASE

Article number	RC582BC
Brand	-
UBB	500613804292
UNSPSC	27112713
EAN	8717659220537
PKG. of 1	Full Box Only

Technical Parameters

Width	40
Height	57
Length	155
Max. operation pressure	6.3
Tool insertion	3/8 inch
Idle rotational speed	850
Air inlet device-sided	R 1/4 inch
Max. loosening torque	40
Max. tightening torque	40
Ratcheting model	Yes
Impulse driver	Yes
Max. thread size (metric)	40
Air volume required	114

Standards