



IMPULSE WRENCH 1/2 RRI-100

Article number	RRI-100RED
Brand	-
UBB	500619066607
UNSPSC	27112713
EAN	8717981204007
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	1/2 inch
Idle rotational speed	5300
Air inlet device-sided	R 1/4 inch
Max. loosening torque	120
Max. tightening torque	120
Attract torque adjustable	Yes
Impulse driver	Yes
Max. thread size (metric)	14
Air volume required	522

Standards