

Fabory Jobber drill
Cylindrical DIN 338 RN HSS
Black 3,0 MM



Article number	U0000.030.001
Brand	-
UBB	240201331537
UNSPSC	23241639
EAN	8715494649735
PKG. of 10	Full Box Only

Technical Parameters

Total length	61
Diameter drill	3
Holding system	Cylindrical plug-in axle
Cutting length	33
Suitable for steel	Yes
Cutting material	HSS
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

