

Fabory Jobber drill
Cylindrical DIN 338 RN HSS
Black 3,7 MM



Article number	U0000.037.001
Brand	-
UBB	240201332295
UNSPSC	23241639
EAN	8715494649810
PKG. of 1	Full Box Only

Technical Parameters

Total length	70
Diameter drill	3.7
Holding system	Cylindrical plug-in axle
Cutting length	39
Suitable for steel	Yes
Cutting material	HSS
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

