

Fabory Jobber drill Cylindrical DIN 338 HSSG Blanc 3,0 MM



Article No.	U0001.030.001
Brand	-
UBB	240201381037
UNSPSC	23241639
EAN	8715494651547
PKG. of 10	Full Box Only

Technical Parameters

Basic material	HSSG
d ₁	3
Diameter (mm)	3
Drill depth	33
Drill point angle	118
Coating	Blanc
Cutting direction	Right
Finish	Bright
Finish	Hell
Finish	luminos
Finish	Jasne
Finish	Brillante
Finish	Brillant
Finish	Bright
Finish	Blank
Finish	Fényes
Finish	Brilhante
Finish	bystrý
Useful length	33
L ₁	61
L ₂	33
Total length (mm)	61
Shank type	Cylindrical

Standards

DIN	338
-----	-----

Type	Cylindrical
Info	Right hand cutting, ground drills according to DIN 338-RN, with a drilling point 118° and a helix angle $20-30^\circ$ (type C) according to DIN 1412.

Technical Specification

Technical Drawing

