

Fabory Jobber drill Cylindrical DIN 338 HSSG Blanc 6,2 MM



Article number U0001.062.001

Brand -

UBB 240201384833

UNSPSC 23241639

EAN 8715494651929

PKG. of 10 Full Box Only

Technical Parameters

Total length	101
Diameter drill	6.2
Holding system	Cylindrical plug-in axle
Cutting length	63
Suitable for steel	Yes
Cutting material	Other
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

