

Fabory Jobber drill Cylindrical DIN 338 HSS Co 5 Golden brown 4,0 MM



Article number	U0002.040.001
Brand	-
UBB	240201343342
UNSPSC	23241639
EAN	8715494653183
PKG. of 10	Full Box Only

Technical Parameters

Total length	75
Diameter drill	4
Holding system	Cylindrical plug-in axle
Cutting length	43
Suitable for stainless steel	Yes
Suitable for steel	Yes
Tip angle	135
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

