

Fabory Jobber drill # DIN 1897 HSSG 3,0 MM



Article number	U0025.030.001
Brand	-
UBB	407201052591
UNSPSC	23241639
EAN	8715494657167
PKG. of 10	Full Box Only

Technical Parameters

Total length	46
Diameter drill	3
Holding system	Cylindrical plug-in axle
Cutting length	16
Cutting material	Other
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

