

## Hexagon head cap screw UNC ASME B18.2.1 Steel SAE J429 Plain Gr.5 1/4-20X3.3/4

|                |                 |
|----------------|-----------------|
| Article number | U01000.025.0375 |
| Brand          | -               |
| UBB            | 500620664648    |
| UNSPSC         | 31161620        |
| EAN            | 8717077333062   |
| PKG. of 50     | Full Box Only   |

### Technical Parameters

|                    |                            |
|--------------------|----------------------------|
| Diameter           | 1/4 Inch                   |
| Length             | 3.3/4 Inch                 |
| Class              | Gr.5                       |
| Driving features   | Hexagon                    |
| Head shape         | Hexagon head               |
| Material           | Steel                      |
| Material technical | SAE J429                   |
| Thread direction   | Right                      |
| Surface treatment  | Plain                      |
| Thread             | Unified National<br>Coarse |
| Threads per inch   | 20                         |
| Info               | ft = fully threaded        |

### Standards

|      |         |
|------|---------|
| BS   | ≈1768   |
| ASME | B18.2.1 |

### Technical Specification

|                     |         |
|---------------------|---------|
| F                   | 0.4375  |
| H                   | 0.15625 |
| LT (min.): L6 Inch  | 1       |
| LT (min.): L≤6 Inch | 0.75    |

### Technical Drawing

