



Fabory Hand tap set DIN ≈352 HSS-G NR. 4

Article No.	U0608.028.001
Brand	-
UBB	240202465003
UNSPSC	23241615
EAN	
PKG. of 1	Full Box Only

Technical Parameters

a □	2.7
Basic material	HSS-G
d ₁	NO. 4
d ₂	3.50
Diameter (inch)	NO.4
Drive size	2.7
Useful length	12
L ₁	40
L ₂	12
Total length (mm)	40
Size (inch)	UNC No. 4 x 40
Threads per inch	40
Tolerance	2B

Info

Set of 3 taps.
UNC screw thread according to ANSI B1.1. No.1-64 through 1/4 with reinforced shank and 5/16 up to 2.IN. with reduced shank. Bright ground and straight flutes, for through holes and blind holes in alloy steel with tensile strength up to 750 N/mm².

Standards

DIN ≈352

Technical Specification

FABORY OF COURSE.

SETTING THE STANDARD
IN FASTENING SOLUTIONS

Technical Drawing

