



**Hexagon socket head cap  
screw UNF 1960 series  
ASME B18.3 Alloy steel  
ASTM A574 Plain #10-32X1  
Inch**

Article number	U07040.019.0100
Brand	-
UBB	500620966514
UNSPSC	31161605
EAN	8717077363342
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	NO.10
Length	1 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine

Info

Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen embrittlement.ft = fully threaded

**Standards**

ASME	B18.3
------	-------

Technical Specification

A	0.312
H	0.19
J	0.15625
LT (min.)	0.88
Threads per inch	32

Technical Drawing

