



**Hexagon socket head  
cap screw UNF 1960  
series ASME B18.3 Alloy  
steel ASTM A574 Plain  
#10-32X1.1/4**

Article number	U07040.019.0125
Brand	-
UBB	500620966779
UNSPSC	31161605
EAN	8717077363366
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	NO.10
Length	1.1/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine

Info

Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen embrittlement.ft = fully threaded

**Standards**

ASME	B18.3
------	-------

Technical Specification

A	0.312
H	0.19
J	0.15625
LT (min.)	0.88
Threads per inch	32

Technical Drawing

