



**Hexagon socket head
cap screw UNF 1960
series ASME B18.3 Alloy
steel ASTM A574 Plain
1.1/2-12X12 Inch**

Article number	U07040.150.1200
Brand	-
UBB	500620990100
UNSPSC	31161605
EAN	8717077365704
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/2 Inch
Length	12 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine

Info Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen embrittlement.ft = fully threaded

Standards

ASME	B18.3
------	-------

Technical Specification

A	2.25
H	1.5
J	1
LT (min.)	3.75
Threads per inch	12

Technical Drawing

