



**Hexagon socket head cap
screw UNF 1960 series
ASME B18.3 Alloy steel
ASTM A574 Zinc plated
#10-32X1/4 ft**

Article number	U07041.019.0025
Brand	-
UBB	500625360457
UNSPSC	31162400
EAN	8715492886798
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.10
Length	1/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Fine

Info

Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen embrittlement.ft = fully threaded

Standards

ASME	B18.3
------	-------

Technical Specification

A	0.312
H	0.19
J	0.15625
LT (min.)	0.88
Threads per inch	32

Technical Drawing

