



## Hexagon socket head shoulder screw UNC ASME B18.3 Alloy steel Plain (#10)1/4X1 Inch

Article number	U07111.025.0100
Brand	-
UBB	500624163472
UNSPSC	31161605
EAN	8715492891419
PKG. of 10	Full Box Only

### Technical Parameters

Length	1 Inch
Driving features	Hexagon socket
Head shape	Cylindrical Knurled
Material	Alloy steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

#### Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems.

### Standards

ASME	B18.3
BS	2470

### Technical Specification

A (max.)	0.375
D	0.25

### Technical Drawing

D1	0.19
E	0.375
H (max.)	0.188
J	0.125
Threads per inch	24
D (min.)	0.246
D (max.)	0.248

