



## Hexagon socket head shoulder screw UNC ASME B18.3 Alloy steel Plain (3/8)1/2X2 1/2

Article number	U07111.050.0250
Brand	-
UBB	500624168919
UNSPSC	31161605
EAN	8715492892171
PKG. of 5	Full Box Only

### Technical Parameters

Length	2.1/2 Inch
Driving features	Hexagon socket
Head shape	Cylindrical Knurled
Material	Alloy steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

#### Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems.

### Standards

ASME	B18.3
BS	2470

### Technical Specification

A (max.)	0.75
D	0.5

### Technical Drawing

D1	0.375
E	0.625
H (max.)	0.312
J	0.25
Threads per inch	16
D (min.)	0.496
D (max.)	0.498

