



**Hexagon socket button head
screw UNC ASME B18.3
Alloy steel ASTM F835 Zinc
plated #4-40X1/4**

Article number	U07151.011.0025
Brand	-
UBB	500621001642
UNSPSC	31161518
EAN	8715492888907
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.4
Length	1/4 Inch
Driving features	Hexagon socket
Head shape	Button head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.

Technical Specification

A	0.213
H	0.059
J	0.0625
Threads per inch	40

Technical Drawing

