



**Hexagon socket button head
screw UNC ASME B18.3
Alloy steel ASTM F835 Zinc
plated 5/16-18X1 Inch**

| | |
|----------------|-----------------|
| Article number | U07151.031.0100 |
| Brand | - |
| UBB | 500621004539 |
| UNSPSC | 31161518 |
| EAN | 8715492889195 |
| PKG. of 50 | Full Box Only |

Technical Parameters

| | |
|--------------------|----------------------------|
| Diameter | 5/16 Inch |
| Length | 1 Inch |
| Driving features | Hexagon socket |
| Head shape | Button head |
| Material | Alloy steel |
| Material technical | ASTM F835 |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Unified National Coarse |

Standards

| | |
|------|-------|
| ASME | B18.3 |
|------|-------|

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.

Technical Specification

| | |
|------------------|--------|
| A | 0.547 |
| H | 0.166 |
| J | 0.1875 |
| Threads per inch | 18 |

Technical Drawing

