



**Hexagon socket button head
screw UNC ASME B18.3
Alloy steel ASTM F835 Zinc
plated 3/8-16X1.1/2**

Article number	U07151.037.0150
Brand	-
UBB	500621005296
UNSPSC	31161518
EAN	8715492889270
PKG. of 25	Full Box Only

Technical Parameters

Diameter	3/8 Inch
Length	1.1/2 Inch
Driving features	Hexagon socket
Head shape	Button head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info	All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.
------	---

Technical Specification

A	0.656
H	0.199
J	0.21875
Threads per inch	16

Technical Drawing

