



**Hexagon socket
countersunk head screw
UNC ASME B18.3 Alloy
steel ASTM F835 Plain
3/8-16X2.1/4**

Article number	U07410.037.0225
Brand	-
UBB	500621022937
UNSPSC	31161518
EAN	8717077366992
PKG. of 25	Full Box Only

Technical Parameters

Diameter	3/8 Inch
Length	2.1/4 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

A	0.781
H	0.234
J	0.21875
LT (min.)	1.25
Threads per inch	16

Technical Drawing

