



**Hexagon socket
countersunk head screw
UNC ASME B18.3 Alloy
steel ASTM F835 Plain
3/8-16X3.1/2**

| | |
|----------------|-----------------|
| Article number | U07410.037.0350 |
| Brand | - |
| UBB | 500621023356 |
| UNSPSC | 31161518 |
| EAN | 8717077367036 |
| PKG. of 10 | Full Box Only |

Technical Parameters

| | |
|--------------------|-------------------------|
| Diameter | 3/8 Inch |
| Length | 3.1/2 Inch |
| Driving features | Hexagon socket |
| Head shape | Countersunk head |
| Material | Alloy steel |
| Material technical | ASTM F835 |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Unified National Coarse |

Standards

| | |
|------|-------|
| ASME | B18.3 |
|------|-------|

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

| | |
|------------------|---------|
| A | 0.781 |
| H | 0.234 |
| J | 0.21875 |
| LT (min.) | 1.25 |
| Threads per inch | 16 |

Technical Drawing

