



**Hexagon socket
countersunk head screw
UNC ASME B18.3 Alloy steel
ASTM F835 Plain 1.-8X4.1/2**

Article number	U07410.100.0450
Brand	-
UBB	500621032910
UNSPSC	31161518
EAN	8717077367968
PKG. of 5	Full Box Only

Technical Parameters

Diameter	1 Inch
Length	4.1/2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

FABORY cause thread fit problems.

Technical Specification

A	1.938
H	0.54
J	0.625
LT (min.)	2.5
Threads per inch	8

Technical Drawing

