



**Hexagon socket
countersunk head screw
UNF ASME B18.3 Alloy steel
ASTM F835 Plain #0-80X1/2
ft**

Article number	U07566.006.0050
Brand	-
UBB	500621042083
UNSPSC	31161518
EAN	8717077368712
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.0
Length	1/2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine

Info
ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

Standards

ASME	B18.3
------	-------

FABORY cause thread fit problems.

Technical Specification

A	0.138
H	0.044
J	0.035
LT (min.)	0.5
Threads per inch	80

Technical Drawing

