



Hexagon socket countersunk head screw UNF ASME B18.3 Alloy steel ASTM F835 Zinc plated #10-32X7/8

Article number	U07567.019.0087
Brand	-
UBB	500625367304
UNSPSC	31162400
EAN	8715492887504
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.10
Length	7/8 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Fine

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.

Standards

ASME	B18.3
------	-------

Technical Specification

A	0.411
H	0.127
J	0.125
LT (min.)	0.88
Threads per inch	32

Technical Drawing

