



## Fabory Die nut HSS-G 1 Inch

|                |               |
|----------------|---------------|
| Article number | U1660.254.001 |
|----------------|---------------|

|       |   |
|-------|---|
| Brand | - |
|-------|---|

|     |              |
|-----|--------------|
| UBB | 240203272762 |
|-----|--------------|

|        |          |
|--------|----------|
| UNSPSC | 27110000 |
|--------|----------|

|     |  |
|-----|--|
| EAN |  |
|-----|--|

|           |               |
|-----------|---------------|
| PKG. of 1 | Full Box Only |
|-----------|---------------|

### Technical Parameters

|                  |            |
|------------------|------------|
| Basic material   | HSS-G      |
| Diameter (inch)  | 1 Inch     |
| h                | 22         |
| s                | 50         |
| Size (inch)      | UNC 1" x 8 |
| Threads per inch | 8          |

|      |  |
|------|--|
| Info | Unified (ISO) screw thread coarse series -UNC- according to ANSI B1.1. Bright ground. Suitable for cleaning and repairing damaged threads, or for cutting threads in difficult to reach spots in alloyed steel with tensile strength up to 750 N/mm <sup>2</sup> . Hexagonal |
|------|--|

### Standards

|     |     |
|-----|-----|
| DIN | 382 |
|-----|-----|

### Technical Specification

### Technical Drawing

**FABORY** *OF COURSE.*  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS

