



## Machine screw round hd slt/ ph comb UNC asme B18.6.3 ASME B18.6.3 Low carbon steel Zinc plated #6-32X7/8

Article number	U24212.013.0087
Brand	-
UBB	500624922158
UNSPSC	31161504
EAN	8712423000513
PKG. of 100	Full Box Only

### Technical Parameters

Diameter	NO.6
Length	7/8 Inch
Driving features	Slotted/Phillips Combination
Head shape	Round head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32
Info	Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME	B18.6.3
------	---------

### Technical Specification

A (max.)	0.26
----------	------

### Technical Drawing

H (max.)	0.103
----------	-------

J (max.)	0.048
----------	-------

No. cross recess	2
------------------	---

T (max.)	0.068
----------	-------

