



**Machine screw round hd slt/  
ph comb UNC asme B18.6.3  
ASME B18.6.3 Low carbon  
steel Zinc plated #6-32X1  
Inch**

Article number	U24212.013.0100
Brand	-
UBB	500624922232
UNSPSC	31161504
EAN	8712423000520
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	NO.6
Length	1 Inch
Driving features	Slotted/Phillips Combination
Head shape	Round head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32

Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

**Standards**

ASME	B18.6.3
------	---------

A (max.)	0.26
H (max.)	0.103
J (max.)	0.048
No. cross recess	2
T (max.)	0.068

