



Machine screw pan head slot UNC asme B18.6.3 ASME B18.6.3 Low carbon steel Zinc plated #2-56X1/4

Article number	U24520.008.0025
Brand	-
UBB	500624931068
UNSPSC	31161504
EAN	8717077794535
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.2
Length	1/4 Inch
Driving features	Slotted
Head shape	Pan head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	56

Info
Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME B18.6.3

Technical Specification

A (max.)	0.167
H (max.)	0.053

Technical Drawing

J (max.)	0.031
T (max.)	0.031

FABORY

