



**Machine screw flat
countersunk slot UNC asme
B18.6.3 ASME B18.6.3 Low
carbon steel Zinc plated
1/4-20X3.**

Article number	U24540.025.0300
Brand	-
UBB	500624950027
UNSPSC	31161504
EAN	8715492973771
PKG. of 100	Full Box Only

Technical Parameters

Diameter	1/4 Inch
Length	3 Inch
Driving features	Slotted
Head shape	Countersunk head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	20

Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.
------	---

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.477
----------	-------

Technical Drawing

H (max.) 0.153

J (max.) 0.075

T (max.) 0.07

