

Spring-type straight pin
slotted ASME ASME B18.8.2
Spring steel SAE 1070 Plain
1/16X3/8



Article number	U39100.006.0037
Brand	-
UBB	500626271414
UNSPSC	31162400
EAN	8712423094253
PKG. of 100	Full Box Only

Technical Parameters

Length	3/8 Inch
A (nom.)	0.0625
Material	Spring steel
Material technical	SAE 1070
Surface treatment	Plain

Info	Warning: electroplating of these products may cause hydrogen embrittlement.V = minimum double shear load in lb.
------	---

Standards

ASME	B18.8.2
------	---------

Technical Specification

A (max.)	0.069
B (max.)	0.059
C (ref.)	0.028
A (min.)	0.066
F	0.012
V	430

Technical Drawing

