



Hexagon socket head shoulder screw UNC ASME B18.3 Stainless steel ASTM F879 304 (1/4)5/16X1/4

Article number	U51044.031.0025
Brand	-
UBB	500624176185
UNSPSC	31161605
EAN	8715492895813
PKG. of 5	Full Box Only

Technical Parameters

Length	1/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical Knurled
Material	Stainless steel
Material technical	ASTM F879 304
Thread direction	Right
Thread	Unified National Coarse

Info

All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems.

Standards

ASME	B18.3
BS	2470

Technical Specification

A (max.)	0.438
D	0.3125

Technical Drawing

D1	0.25
E	0.438
H (max.)	0.219
J	0.15625
Threads per inch	20
D (min.)	0.3085
D (max.)	0.3105

