



## Hexagon socket head shoulder screw UNC ASME B18.3 Stainless steel ASTM F879 304 (5/16)3/8X3/4

|                |                 |
|----------------|-----------------|
| Article number | U51044.037.0075 |
| Brand          | -               |
| UBB            | 500624177332    |
| UNSPSC         | 31161605        |
| EAN            | 8715492895967   |
| PKG. of 5      | Full Box Only   |

### Technical Parameters

|                        |  |
|------------------------|--|
| D                      | 3/8  |
| D <sub>1</sub>         | 5/16-18  |
| Length (L) (Inch - ft) | 3/4  |
| Info                   | All dimensions in above table are in inches. Marking of these screws is not mandatory. Due to the unfavourable head geometry these fasteners have reduced loadability. Attention: As the thread tolerance class for these screws is 3A, plating can cause thread fit problems. |
| Driving features       | Hexagon socket   |
| Head shape             | Cylindrical Knurled  |
| Material               | Stainless steel  |
| Material technical     | ASTM F879 304  |
| Thread direction       | Right  |
| Thread                 | Unified National Coarse  |

### Standards

|      |       |
|------|-------|
| BS   | 2470  |
| ASME | B18.3 |

|                  |         |
|------------------|---------|
| A (max.)         | 0.562   |
| D <sub>1</sub>   | 5/16-18 |
| E                | 0.500   |
| H (max.)         | 0.250   |
| J                | 3/16    |
| Threads per inch | 18      |
| D (min.)         | 0,3710  |
| D (max.)         | 0,3730  |

**FABORY**  
DE CALIBRE

