



## Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #2-56X5/8

|                |                 |
|----------------|-----------------|
| Article number | U51122.008.0062 |
| Brand          | -               |
| UBB            | 500625001085    |
| UNSPSC         | 31161504        |
| EAN            | 8717077793439   |
| PKG. of 100    | Full Box Only   |

### Technical Parameters

|                    |                            |
|--------------------|----------------------------|
| Diameter           | NO.2                       |
| Length             | 5/8 Inch                   |
| Driving features   | Phillips                   |
| Head shape         | Pan head                   |
| Material           | Stainless steel            |
| Material technical | ASTM F837 304              |
| Thread direction   | Right                      |
| Thread             | Unified National<br>Coarse |
| Threads per inch   | 56                         |

Info

Screws with diameter  $\leq$  No.5 and length  $\leq$  1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length  $\leq$  2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME B18.6.3

### Technical Specification

|          |       |
|----------|-------|
| A (max.) | 0.167 |
| H (max.) | 0.062 |

### Technical Drawing

**FABORY**

