



## Machine screw oval countersunk UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) 1/4-20X1.3/4

Article number	U51320.025.0175
Brand	-
UBB	500625049449
UNSPSC	31161504
EAN	8717077792630
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	1/4 Inch
Length	1.3/4 Inch
Driving features	Phillips
Head shape	Countersunk oval
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	20

Info

Screws with diameter  $\leq$  No.5 and length  $\leq$  1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length  $\leq$  2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME	B18.6.3
------	---------

### Technical Specification

A (max.)	0.477
----------	-------

### Technical Drawing

C	0.079
H (max.)	0.153
No. cross recess	3

