



Hexagon socket countersunk head screw UNF ASME B18.3 Stainless steel ASTM F879 304 CW / CW1 #10-32X5/16 ft

Article number	U51566.019.0031
Brand	-
UBB	500621338689
UNSPSC	31161518
EAN	8717077394292
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.10
Length	5/16 Inch
Class	CW / CW1
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	ASTM F879 304
Thread direction	Right
Thread	Unified National Fine

Info

ft = fully threaded
All dimensions in
above table are in
inches. Marking of
these screws is not
mandatory. Due to
the unfavourable
head geometry
these fasteners
have reduced
loadability. Attention:
As the thread
tolerance class for
thread sizes up to
and including 1 inch
is 3A, plating can

Standards

ASME	B18.3
------	-------

FABORY cause thread fit problems.

Technical Specification

A	0.411
H	0.127
J	0.125
LT (min.)	0.88
Threads per inch	32

Technical Drawing

