



**Hexagon socket  
countersunk head screw  
UNF ASME B18.3 Stainless  
steel ASTM F879 304 CW /  
CW1 #10-32X3/4 ft**

|                |                 |
|----------------|-----------------|
| Article number | U51566.019.0075 |
| Brand          | -               |
| UBB            | 500621339182    |
| UNSPSC         | 31161518        |
| EAN            | 8717077394346   |
| PKG. of 100    | Full Box Only   |

**Technical Parameters**

|                    |                       |
|--------------------|-----------------------|
| Diameter           | NO.10                 |
| Length             | 3/4 Inch              |
| Class              | CW / CW1              |
| Driving features   | Hexagon socket        |
| Head shape         | Countersunk head      |
| Material           | Stainless steel       |
| Material technical | ASTM F879 304         |
| Thread direction   | Right                 |
| Thread             | Unified National Fine |

Info

ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

**Standards**

|      |       |
|------|-------|
| ASME | B18.3 |
|------|-------|

**FABORY** cause thread fit problems.

**Technical Specification**

|                  |       |
|------------------|-------|
| A                | 0.411 |
| H                | 0.127 |
| J                | 0.125 |
| LT (min.)        | 0.88  |
| Threads per inch | 32    |

**Technical Drawing**

