



Machine screw truss UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #4-40X3/8

Article number	U51862.011.0037
Brand	-
UBB	500625056287
UNSPSC	31161504
EAN	8712423001138
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.4
Length	3/8 Inch
Driving features	Phillips
Head shape	Truss head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	40

Info

Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.257
H (max.)	0.069

Technical Drawing

No. cross recess 1

FABORY

