

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M5X100

Article number	01000.050.100
Brand	-
UBB	500644972878
UNSPSC	31161620
EAN	8717077046931
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	100
P	0.8
s	8

Technical Drawing

