

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M8X130

Article number	01000.080.130
Brand	-
UBB	950351005026
UNSPSC	31161620
EAN	8715492007537
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	28
b (min.): $L \leq 125$ mm	22
d-D	M8
k	5.3
L (mm)	130
P	1.25
s	13

Technical Drawing

