

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X45

Article number	01000.100.045
Brand	-
UBB	950351005448
UNSPSC	31161620
EAN	8715492007629
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	45
P	1.5
s	17

Technical Drawing

