

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X70

Article number	01000.100.070
Brand	-
UBB	950351005935
UNSPSC	31161620
EAN	8715492007674
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L \geq 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	70
P	1.5
s	17

Technical Drawing

