

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X80

Article number	01000.100.080
Brand	-
UBB	950351006198
UNSPSC	31161620
EAN	8715492007698
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L \geq 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	80
P	1.5
s	17

Technical Drawing

