

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X100

Article number	01000.100.100
Brand	-
UBB	950351006438
UNSPSC	31161620
EAN	8715492007735
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	100
P	1.5
s	17

Technical Drawing

