

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X150

Article number	01000.100.150
Brand	-
UBB	950351006925
UNSPSC	31161620
EAN	8715492007797
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	150
P	1.5
s	17

Technical Drawing

