

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M10X170

Article number	01000.100.170
Brand	-
UBB	952351313566
UNSPSC	31161620
EAN	8715492007834
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	170
P	1.5
s	17

Technical Drawing

